



EC350

### 3Ph Kwhmeter direct 63A

#### Technical Features

##### Architecture

Type of pole	3P+N
--------------	------

##### Electric current

Rated current	63 A
---------------	------

##### Capacity

Number of modules	4
-------------------	---

##### Connectivity

Type of connection	Direct connection
--------------------	-------------------

##### Dimensions

Height	90 mm
Width	72 mm

##### Equipment

Type of pulse generator	Electrical
-------------------------	------------

##### Compatibility

Suitable for	Purchase
--------------	----------

##### Installation, mounting

Mounting on	DIN rail
-------------	----------

##### Measurement

Measuring system	Direct measurement
Type of measuring instrument	Electronic
Frequency measuring range	50 - 60 Hz

##### Power supply

Number of phases for power supply	4
-----------------------------------	---

##### Functions

Accuracy class	B
Tariff type	One-tariff

##### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

##### Use conditions

Operating temperature	-10 - 55 °C
Storage/transport temperature	-25 - 70 °C

##### Power

Power consumption VA	8.40 VA
Total power loss under IN	1.80 W

##### Electric current

Maximum measuring circuit current	63 A
-----------------------------------	------

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes