



CDA516D

**RCCB 1P+N 16A 30mA A**

**Technical Features**

**Architecture**

Type of pole	1P+N
--------------	------

**Electric current**

Rated current	16 A
Rated residual operating current Idn	30 mA
Breaking and opening capacity Idm	1.25 kA
Rated conditional short-circuit current I <sub>nc</sub> according to EN61008-1	10 kA
Rated current -25°C	16 A
Rated current at -20°C	16 A
Rated current at -15°C	16 A
Rated current at -10°C	16 A
Rated current at -5°C	16 A
Rated current at 0°C	16 A
Rated current 5°C	16 A
Rated current 10°C	16 A
Rated current 15°C	16 A
Rated current at 20°C	16 A
Rated current 25°C	16 A
Rated current 30°C	16 A
Rated current 35°C	16 A
Rated current at 40°C	16 A
Rated current at 45°C	16 A
Rated current at 50°C	16 A
Rated current 55°C	16 A
Rated current 60°C	16 A
Rated current 65°C	16 A
Rated current 70°C	16 A

**Installation, mounting**

Nominal tightening torque top terminal	3.60 - 3.60 Nm
Nominal tightening torque down terminal	3.60 - 3.60 Nm

**Voltage**

Rated operational voltage Ue	230 - 230 V
Type voltage supply	AC
Rated insulation voltage Ui	500 V
Dielectric strength value of power frequency	2 kV
Rated impulse withstand voltage U <sub>imp</sub>	4000 V
Rated impulse withstand voltage U <sub>imp</sub> IEC 60947-3	6000 V
Max. operating voltage	253 V

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Capacity**

Number of modules	2
-------------------	---

**Compatibility**

Suitable for DIN Rail	Yes
-----------------------	-----

**Safety**

Residual current type	A
Ingress Protection (IP) class	IP20

**Installation, mounting**

Type of top connection for modular devices	Screw terminal
Type of bottom connection for modular devices	biconnect

**Connection**

Cross-section of output with screws, for massive conductors	1 - 25 mm <sup>2</sup>
Cross-section of output with screws, for flexible conductors	1 - 16 mm <sup>2</sup>

**Power**

Total power loss under IN	0.51 W
---------------------------	--------

**Use conditions**

Max. Altitude	2000 m
Operating temperature	-25 - 70 °C

**Endurance**

Electric endurance in number of cycles	10000
Number of mechanical operations	20000

**Connectivity**

Type of connection	Screw terminal
Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal

**Dimensions**

Height	85 mm
Width	36 mm
Depth	70 mm

**Sustainability**

RoHS conform	Yes
--------------	-----

**Illustrations | Drawings**

