



ADC332T

**RCBO Electronic 1P 6kA C-32A 30mA A Class 1M**

**Technical Features**

**Architecture**

Type of pole	1P
Number of protected poles	1
Curve	C

**Electric current**

Rated current	32 A
Rated residual operating current I <sub>dn</sub>	30 mA
Rated current -25°C	43.61 A
Rated current at -20°C	42.79 A
Rated current -15°C	41.96 A
Rated current -10°C	42 A
Rated current -5°C	40.32 A
Rated current at 0°C	39.50 A
Rated current 5°C	38.68 A
Rated current 10°C	37.86 A
Rated current 15°C	37.04 A
Rated current at 20°C	36.21 A
Rated current 25°C	35.39 A
Rated current 30°C	32 A
Rated current 35°C	33.75 A
Rated current at 40°C	32.93 A
Rated current at 50°C	33 A
Rated current 55°C	30.46 A
Rated current 60°C	29.64 A
Correction factor of rating current for 2 devices placed side by side	0.95
Correction factor of rating current for 3 devices placed side by side	0.95
Correction factor of rating current for 4 and 5 devices placed side by side	0.90
Correction factor of rating current for 6 devices placed side by side	0.85
Min./max. threshold value of the AC thermal operation	1.13 - 1.45 A

**Safety**

Residual current type	A
Ingress Protection (IP) class	IP2X

**Main electrical attributes**

Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1	6 kA
---	------

**Voltage**

Rated insulation voltage U <sub>i</sub>	250 V
Rated impulse withstand voltage U <sub>imp</sub>	4000 V
Max. operating voltage	253 V
Rated operational voltage U <sub>e</sub>	240 - 240 V
Overvoltage category according to IEC 60947-1	3

**Power**

Total power loss under I <sub>N</sub>	7.08 W
---------------------------------------	--------

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Use conditions**

Max. altitude	2000 m
Class of energy limitation I <sup>2</sup> t	3

**Endurance**

Electric endurance in number of cycles	8000
Number of mechanical operations	20000

---

**Connection**

Cross-section of input with screws, for flexible conductors	1 - 10 mm <sup>2</sup>
Cross-section of input with screws, for massive conductors	1 - 16 mm <sup>2</sup>

**Capacity**

Number of modules	1
-------------------	---

**Installation, mounting**

Type of top connection for modular devices	Screw terminal
Type of bottom connection for modular devices	Screw terminal

**Dimensions**

Height	92 mm
Width	17.70 mm
Depth	70 mm

**Use conditions**

Operating temperature	-20 - 70 °C
Storage/transport temperature	-25 - 80 °C

**Connection**

Cross-section of output with screws, for flexible conductors	1 - 16 mm <sup>2</sup>
Cross-section of output with screws, for massive conductors	1 - 16 mm <sup>2</sup>

**Compatibility**

Suitable for DIN Rail	Yes
-----------------------	-----

**Sustainability**

RoHS conform	Yes
--------------	-----