



JVC4800S25TW

**250A TPN board, INVICTA, 48P Chassis , ISO-STD-GR**

**Technical Features**

**Connection**

Number of accessible phases	48
-----------------------------	----

**Installation, mounting**

Mounting on	Surface mounting
-------------	------------------

**Electric current**

Rated current	250 A
Breaking and opening capacity I <sub>dm</sub>	0 kA

**Equipment**

With lock	Yes
Has mounting plate	No
Equipped with switch	Isolator
Number of switches	1
Type of busbar chassis	Fixed load chassis

**Capacity**

Number of modules	16
-------------------	----

**Dimensions**

Height	1000 mm
Width	480 mm
Depth	135 mm

**Cover, door**

Door/cover is transparent	No
---------------------------	----

**Materials**

Material	Steel
RAL code	7035
Colour	Light grey

**Safety**

Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP30
Locking type	Key lock With lock

**Architecture**

Number of poles	48
-----------------	----

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes