



WNE040B

cubyko 2-gang 2-way switch flush mounted white IP55

Technical Features

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	Pure white
RAL code	9010
Surface finish	Matt Satin finish
Material	Polypropylene (PP)

Identification

Assembly arrangement	Mechanism with upper casing
----------------------	-----------------------------

Connectivity

Mounting type	Screw mounting
---------------	----------------

Dimensions

Dimensions	75 x 75 mm
Built-in depth flush-mounted boxes	40 mm

Safety

Ingress Protection (IP) class	IP55
Impact resistance IK	IK07

Electric current

Rated current	10 A
---------------	------

Connection

Type of contacts	2-way
------------------	-------

Texts

Lighting	Without lighting (cannot be illuminated)
Switch mode	2-way

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes