



MU363A

**MCB 3P 6kA C-63A 3M**

**Technical Features**

**Electric current**

Rated current	63 A
Rated current -15°C	76.20 A
Rated current -10°C	74.90 A
Rated current -5°C	73.50 A
Rated current at 0°C	72.10 A
Rated current 5°C	70.70 A
Rated current 10°C	69.20 A
Rated current 15°C	67.70 A
Rated current at 20°C	66.20 A
Rated current 25°C	64.60 A
Rated current 30°C	63 A
Rated current 35°C	61.40 A
Rated current at 40°C	59.70 A
Rated current at 45°C	57.90 A
Rated current at 50°C	56.10 A
Rated current 55°C	54.30 A
Rated current 60°C	52.40 A
Rated current 65°C	50.70 A
Rated current 70°C	48.90 A

**Architecture**

Type of pole	3P
Curve	C

**Capacity**

Number of modules	3
-------------------	---

**Main electrical attributes**

Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	6 kA
---	------

**Installation, mounting**

Nominal tightening torque top terminal	2.80 - 2.80 Nm
Nominal tightening torque down terminal	2.80 - 2.80 Nm

**Voltage**

Rated operational voltage Ue	230 - 400 V
Type voltage supply	AC
Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	4000 V

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Connection**

Cross-section of input and output with screws, for massive conductors	1 - 35 mm <sup>2</sup>
Cross-section of input and output with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for massive conductors	1 - 35 mm <sup>2</sup>
Cross-section flexible conductor	1 - 25 mm <sup>2</sup>
Cross-section rigid conductor	1 - 35 mm <sup>2</sup>

**Installation, mounting**

Nominal tightening torque	2.80 - 2.80 Nm
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal
360° mounting position possible	Yes

# Product Datasheet

## MU363A

---

### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

### Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	2
Class of energy limitation I <sup>2</sup> t	3
Air humidity protection	For all climates
Operating temperature	-25 - 70 °C

### Power

Total power loss under IN	18.10 W
---------------------------	---------

### Connectivity

Type of connection	Screw terminal
Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal

### Dimensions

Height	83 mm
Width	52.50 mm
Depth	70 mm

### Sustainability

RoHS conform	Yes
--------------	-----