



JKD11111

**Dual Metered, Dual Row 22way 100A MID Pulsed, Modbus**

**Technical Features**

**Installation, mounting**

|             |                  |
|-------------|------------------|
| Mounting on | Surface mounting |
|-------------|------------------|

**Architecture**

|                 |   |
|-----------------|---|
| Number of poles | 2 |
|-----------------|---|

**Functions**

|                            |     |
|----------------------------|-----|
| Has protection main switch | Yes |
|----------------------------|-----|

**Capacity**

|                   |    |
|-------------------|----|
| Number of modules | 22 |
|-------------------|----|

**Electric current**

|               |       |
|---------------|-------|
| Rated current | 100 A |
|---------------|-------|

**Dimensions**

|        |        |
|--------|--------|
| Depth  | 125 mm |
| Height | 472 mm |
| Width  | 398 mm |

**Cover, door**

|                           |    |
|---------------------------|----|
| Interlockable             | No |
| Door/cover is transparent | No |

**Materials**

|          |              |
|----------|--------------|
| RAL code | 7035<br>9010 |
| Colour   | Light grey   |
| Material | Steel        |

**Connection**

|                             |   |
|-----------------------------|---|
| Number of accessible phases | 2 |
|-----------------------------|---|

**Scope of delivery**

|                             |   |
|-----------------------------|---|
| Number of RCCB in enclosure | 0 |
|-----------------------------|---|

**Equipment**

|                   |     |
|-------------------|-----|
| Number of rows    | 2   |
| With energy meter | Yes |

**Safety**

|                               |       |
|-------------------------------|-------|
| Ingress Protection (IP) class | IP2XC |
|-------------------------------|-------|