



SPB015N

**Cartridge T2 N-PE Uc 260V I<sub>max</sub> 40kA U<sub>p</sub> 1.5kV**

**Technical Features**

**Capacity**

Number of modules	1
-------------------	---

**Voltage**

Rated operational voltage U <sub>e</sub>	240 - 240 V
Continuous operating voltage U <sub>c</sub> according to IEC 61643-1	275 V
Voltage protection level U <sub>p</sub> according to IEC 61643-1	1.50 kV
Voltage protection level U <sub>p</sub> L-PE/N-PE according to IEC 61643-11	1.35 kV
Voltage level U <sub>p</sub> L-N/PEN IEC 61643-11	1500 V

**Electric current**

Nominal discharge current I <sub>n</sub> 8 - 20 μs L-N(PEN)/N-PE IEC 61643	20 kA
Max. discharge (I <sub>max</sub> ) L-N(PEN)/ N-PE	40 kA

**Dimensions**

Height	52.4 mm
Width	17.50 mm
Depth	55.3 mm

**Use conditions**

Operating temperature	-40 - 80 °C
-----------------------	-------------

**Network configuration**

Network type	TN-S TT
--------------	------------

**Connection**

Cross-section of input and output with screws, for flexible conductors	25 - 25 mm <sup>2</sup>
Cross-section of input and output with screws, for massive conductors	35 - 35 mm <sup>2</sup>

**Standards**

Requirement class IEC 61643	T2
-----------------------------	----

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Installation, mounting**

Nominal tightening torque	3 - 3 Nm
---------------------------	----------