



HDA061Z

Moulded Case Circuit Breaker X160 1P 18kA 63A

Technical Features

Electric current

Rated current	63 A
Rated ultimate short-circuit breaking capacity Icu under 240 V AC IEC 60947-2	18 kA
Rated service breaking capacity Ics under 230 V AC according to IEC 60947-2	18 kA
Rated current 10°C according to IEC 60947	76.80 A
Rated current 15°C according to IEC 60947	75.20 A
Rated current 20°C according to IEC 60947	73.60 A
Rated current 25°C according to IEC 60947	71.90 A
Rated current 30°C according to IEC 60947	70.20 A
Rated current at 35°C according to IEC 60947	68.50 A
Rated current at 40°C according to IEC 60947	66.70 A
Rated current 45°C according to IEC 60947	64.80 A
Rated current 50°C according to IEC 60947	63 A
Rated current 55°C according to IEC 60947	61 A
Rated current at 60°C according to IEC 60947	59 A
Rated current 65°C according to IEC 60947	56.90 A
Rated current 70°C according to IEC 60947	54.70 A

Architecture

Number of poles	1
Control/operation element	Toggle
Device construction type	Fixed built-in

Tripping

Response time when opening	10 ms
----------------------------	-------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Voltage

Rated impulse withstand voltage Uimp	8000 V
Rated insulation voltage Ui	690 V

Functions

Trip unit	TM F/F
-----------	--------

Power

Total power loss under IN	5.10 W
---------------------------	--------

Endurance

Electric endurance in number of cycles	10000
Number of mechanical operations	20000

Safety

Ingress Protection (IP) class	IP4X
-------------------------------	------

Connection

Cross-section flexible conductor	4 - 70 mm ²
Cross-section rigid conductor	4 - 95 mm ²

Installation, mounting

Nominal tightening torque	6 - 6 Nm
Mounting-/Connection Position	Front

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Settings

Thermal protection knob setting xIN 1

1

Adjustment range short-term delayed short-circuit release

0 - 0 A

Compatibility

Suitable for DIN Rail

No

Main electrical attributes

Magnetic protection trip time

0 - 0 ms