




HHJ401DR



Moulded Case Circuit Breaker h3 x630 TM ADJ 4P4D N0-100% 400A 25kA FTC

Technical Features

Electric current

Rated current	400 A
Rated ultimate short-circuit breaking capacity I _{cu} under 400 V AC IEC 60947-2	25 kA
Rated ultimate short-circuit breaking capacity I _{cu} under 240 V AC IEC 60947-2	35 kA
Rated service breaking capacity I _{cs} under 230 V AC according to IEC 60947-2	35 kA
Rated service breaking capacity I _{cs} under 400 V AC according to IEC 60947-2	25 kA
Rated current 10°C according to IEC 60947	470.70 A
Rated current 15°C according to IEC 60947	462.50 A
Rated current 20°C according to IEC 60947	454.10 A
Rated current 25°C according to IEC 60947	445.50 A
Rated current 30°C according to IEC 60947	436.80 A
Rated current at 35°C according to IEC 60947	427.90 A
Rated current at 40°C according to IEC 60947	418.80 A
Rated current 45°C according to IEC 60947	409.50 A
Rated current 50°C according to IEC 60947	400 A
Rated current 55°C according to IEC 60947	390.30 A
Rated current at 60°C according to IEC 60947	380.30 A
Rated current 65°C according to IEC 60947	370 A
Rated current 70°C according to IEC 60947	359.40 A

Architecture

Number of poles	4
Control/operation element	Toggle
Device construction type	Fixed built-in
Neutral position	Left

Tripping

Response time when opening	10 ms
----------------------------	-------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Voltage

Rated impulse withstand voltage U _{imp}	8000 V
Rated insulation voltage U _i	800 V
Rated operational voltage U _e	220 - 415 V

Functions

Trip unit	TM A/A
-----------	--------

Power

Total power loss under I _N	80 W
---------------------------------------	------

Safety

Ingress Protection (IP) class	IP4X
-------------------------------	------

Settings

Thermal protection knob setting xI _N	0.63 0.8 1
---	------------------

Cable

Cable material	Copper
----------------	--------

Compatibility

Compatible with RDC AOB	Yes
Suitable for DIN Rail	No
Suitable for distribution board	Yes

Dimensions

Dimensions	260 x 185 mm
Height	260 mm
Width	185 mm
Depth	150 mm
Downstream busbar: width, height, diameter screw (max.)	10 mm
	12 mm
	32 mm
Top stream busbar: width, height, diameter screw (max.)	10 mm
	12 mm
	32 mm

Installation, mounting

Mounting-/Connection Position	Front
Nominal tightening torque	18 - 18 Nm
Nominal tightening torque down terminal	18 - 18 Nm
Nominal tightening torque top terminal	18 - 18 Nm

Sustainability

REACH conform	Yes
RoHS conform	Yes