



HMS101JC

Moulded Case Circuit Breaker h3+ P160 LSI 4P4D N0-50-100% 100A 50kA CTC

Technical Features

Electric current

| | |
|---|---------|
| Rated current | 100 A |
| Rated ultimate short-circuit breaking capacity I _{cu} under 230 V AC IEC 60947-2 | 65 kA |
| Rated ultimate short-circuit breaking capacity I _{cu} under 240 V AC IEC 60947-2 | 65 kA |
| Rated ultimate short-circuit breaking capacity I _{cu} under 400 V AC IEC 60947-2 | 50 kA |
| Rated ultimate short-circuit breaking capacity I _{cu} under 415 V AC IEC 60947-2 | 50 kA |
| Breaking capacity on 1-pole for AC 230 V IEC 60947-2 | 2.50 kA |
| Breaking capacity on 1-pole for AC 400 V IEC 60947-2 | 2.50 kA |

Architecture

| | |
|---------------------------|----------------|
| Number of poles | 4 |
| Control/operation element | Toggle |
| Device construction type | Fixed built-in |
| Neutral position | Left |

Electric current

| | |
|---|-------|
| Rated ultimate short-circuit breaking capacity I _{cu} under 690 V AC IEC 60947-2 | 6 kA |
| Rated service breaking capacity I _{cs} under 220 V AC according to IEC 60947-2 | 65 kA |
| Rated service breaking capacity I _{cs} under 230 V AC according to IEC 60947-2 | 65 kA |
| Rated service breaking capacity I _{cs} under 240 V AC according to IEC 60947-2 | 65 kA |
| Rated service breaking capacity I _{cs} under 380 V AC according to IEC 60947-2 | 50 kA |
| Rated service breaking capacity I _{cs} under 400 V AC according to IEC 60947-2 | 50 kA |
| Rated service breaking capacity I _{cs} under 415 V AC according to IEC 60947-2 | 50 kA |
| Rated service breaking capacity I _{cs} under 690 V AC according to IEC 60947-2 | 6 kA |
| Rated current 10°C according to IEC 60947 | 100 A |
| Rated current 15°C according to IEC 60947 | 100 A |
| Rated current 20°C according to IEC 60947 | 100 A |
| Rated current 25°C according to IEC 60947 | 100 A |
| Rated current 30°C according to IEC 60947 | 100 A |
| Rated current at 35°C according to IEC 60947 | 100 A |
| Rated current at 40°C according to IEC 60947 | 100 A |
| Rated current 45°C according to IEC 60947 | 100 A |
| Rated current 50°C according to IEC 60947 | 100 A |
| Rated current 55°C according to IEC 60947 | 100 A |
| Rated current at 60°C according to IEC 60947 | 100 A |
| Rated current 70°C according to IEC 60947 | 100 A |
| Rated current 65°C according to IEC 60947 | 100 A |

Settings

| | |
|---|-----------------|
| Ir1 current dial setting | 40 A |
| | 45 A |
| | 50 A |
| | 57 A |
| | 63 A |
| | 72 A |
| | 80 A |
| | 87 A |
| | 93 A |
| | 100 A |
| Adjustment range short-term delayed short-circuit release | 54.6 - 1000.0 A |

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

Installation, mounting

| | |
|-------------------------------|----------|
| Nominal tightening torque | 6 - 6 Nm |
| Mounting-/Connection Position | Front |

| | |
|--|------------------------|
| Voltage | |
| Rated impulse withstand voltage Uimp | 8000 V |
| Rated insulation voltage Ui | 800 V |
| Rated operational voltage Ue | 220 - 690 V |
| Functions | |
| Trip unit | LSI |
| Power | |
| Total power loss under IN | 10.50 W |
| Power loss per pole at In | 3.50 W |
| Endurance | |
| Electric endurance in number of cycles | 10000 |
| Number of mechanical operations | 40000 |
| Equipment | |
| Number of auxiliary contacts as change-over contact | 0 |
| Number of auxiliary contacts as normally closed contact | 0 |
| Number of auxiliary contacts as normally open contact | 0 |
| Safety | |
| Ingress Protection (IP) class | IP4X |
| Use conditions | |
| Operating temperature | -25 - 70 °C |
| Connection | |
| Cross-section flexible conductor | 6 - 70 mm ² |
| Cover, door | |
| Interlockable | Yes |
| Connection | |
| Cross-section rigid conductor | 6 - 95 mm ² |
| Cable | |
| Cable material | Copper |
| Use conditions | |
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 3 |
| Dimensions | |
| Height | 130 mm |
| Width | 120 mm |
| Depth | 97 mm |
| Controls and indicators | |
| Motor drive integrated | No |
| Compatibility | |
| Suitable for DIN Rail | No |
| Compatible with RDC AOB | No |
| Suitable for distribution board | Yes |
| Power supply | |
| Position power supply | Bidirectional |
| Connectivity | |
| Type of connection | Screw terminal |

Electrical protection

| | |
|---|-------|
| Long-time overload protection (ltd): delay (tr) | 0.5 s |
| | 1.5 s |
| | 2.5 s |
| | 5 s |
| | 7.5 s |
| | 9 s |
| | 10 s |
| | 12 s |
| | 14 s |
| | 16 s |

| | |
|--|-----|
| Short-time protection (std): current (lsc) | 1.5 |
| | 2 |
| | 3 |
| | 4 |
| | 5 |
| | 6 |
| | 7 |
| | 8 |
| | 10 |

| | |
|--|--------|
| Short-time protection (std): delay (tsd) | 50 ms |
| | 100 ms |
| | 200 ms |
| | 300 ms |
| | 400 ms |

| | |
|---|----|
| Instantaneous protection (li): dial setting coefficient | 3 |
| | 4 |
| | 5 |
| | 6 |
| | 7 |
| | 8 |
| | 10 |
| | 12 |
| | 15 |

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|
