




HAB404

Load break switch 4P 40A

Technical Features

Electric current

Rated current	40 A
Acceptable current rating AC21	40 A
Acceptable current rating AC21 category B	40 A

Architecture

Type of pole	4P
--------------	----

Electric current

Acceptable current rating AC22 category B	40 A
---	------

Architecture

Control/operation element	Short rotary handle
---------------------------	---------------------

Electric current

Acceptable current rating AC23 category A	40 A
Acceptable current rating AC23 category B	40 A

Architecture

Number of poles	4
-----------------	---

Electric current

Rated short-circuit making capacity Icm under 415 V AC according to IEC 60947-3	1.80 kA
Rated short-time withstand current Icw 1s IEC 60947	1.26 kA
Rated short-time withstand current Icw IEC 60947	1.26 kA

Connection

Cross-section rigid conductor	16 mm ²
-------------------------------	--------------------

Voltage

Rated insulation voltage Ui	800 V
Rated impulse withstand voltage Uimp	8000 V
Rated operational voltage Ue	380 - 415 V

Power

Power loss per pole at In	0.90 W
Total power loss under IN	3.60 W
Rated operational power under 400 V AC AC1	26000 W
Rated operational power under 400 V AC AC23	18000 W

Installation, mounting

Nominal tightening torque	2 - 2.2 Nm
---------------------------	------------

Equipment

Motor drive optional	No
Number of auxiliary contacts as change-over contact	0
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0

Use conditions

Operating temperature	-20 - 70 °C
-----------------------	-------------

Cover, door

Interlockable	Yes
---------------	-----

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Connectivity	
Type of connection	Screw terminal
Functions	
Is reversing switch	No
Version as emergency stop installation	No
Version as main switch	Yes
Version as maintenance/service switch	Yes
Version as safety switch	Yes
Version as switch disconnecter compact	Yes
Capacity	
Number of modules	3.42
Sustainability	
REACH-SVHC free	Yes
RoHS conform	Yes

Illustrations | Drawings

