



MU220A

### MCB 2P 6kA C-20A 2M

#### Technical Features

##### Electric current

Rated current	20 A
Rated short-circuit breaking capacity Icn under 230 V AC according to IEC 60898-1	6 kA
Rated current -15°C	26.74 A
Rated current -10°C	26.41 A
Rated current -5°C	25.45 A
Rated current at 0°C	24.81 A
Rated current 5°C	24.17 A
Rated current 10°C	23.52 A
Rated current 15°C	22.88 A
Rated current at 20°C	22.23 A
Rated current 25°C	21.59 A
Rated current 30°C	20 A
Rated current 35°C	20.30 A
Rated current at 40°C	19.66 A
Rated current at 45°C	19.01 A
Rated current at 50°C	19 A
Rated current 55°C	17.73 A
Rated current 60°C	17.08 A
Rated current 65°C	16.44 A
Rated current 70°C	15.79 A

##### Architecture

Type of pole	2P
Curve	C

##### Capacity

Number of modules	2
-------------------	---

##### Main electrical attributes

Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	6 kA
---	------

##### Installation, mounting

Nominal tightening torque top terminal	2.80 - 2.80 Nm
Nominal tightening torque down terminal	2.80 - 2.80 Nm

##### Voltage

Rated operational voltage Ue	400 - 400 V
Type voltage supply	AC
Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	4000 V

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Connection

Cross-section of input and output with screws, for massive conductors	1 - 35 mm <sup>2</sup>
Cross-section of input and output with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for massive conductors	1 - 35 mm <sup>2</sup>
Cross-section flexible conductor	1 - 25 mm <sup>2</sup>
Cross-section rigid conductor	1 - 35 mm <sup>2</sup>

##### Installation, mounting

Nominal tightening torque	2.80 - 2.80 Nm
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal
360° mounting position possible	Yes

**Safety**

Ingress Protection (IP) class

IP20

**Use conditions**

Degree of pollution according to IEC 60664 / IEC 60947-2

2

Class of energy limitation I<sup>2</sup>t

3

Air humidity protection

For all climates

Operating temperature

-25 - 70 °C

**Power**

Total power loss under IN

4.35 W

**Connectivity**

Type of connection

Screw terminal

Top connection alignment for modular devices

Aligned terminal

Down connection alignment for modular devices

Aligned terminal

**Dimensions**

Height

83 mm

Width

35 mm

Depth

70 mm

**Sustainability**

RoHS conform

Yes