



EH211



IP20



### 2 modules daily time switch with reserve with clock hands

#### Technical Features

##### Equipment

Number of channels	1
--------------------	---

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Power

Power consumption during operation	0.50 VA
230 V incandescent and halogen lamp	1000 W
Power incandescent lamp	1000 - 1000 W

##### Functions

Number of function channels	1
-----------------------------	---

##### Connection

Number of contacts	1
Cross-section flexible conductor	1 - 4 mm <sup>2</sup>
Cross-section rigid conductor	1 - 4 mm <sup>2</sup>

##### Use conditions

Operating temperature	-10 - 55 °C
-----------------------	-------------

##### Capacity

Number of modules	2
-------------------	---

##### Dimensions

Height	90 mm
Width	36 mm
Depth	58 mm

##### Texts

Switch mode	Change-over contact, usable as NC or NO
Installation mode	For mounting on DIN rail

##### Electric current

Max. power (cos phi 0,6)	3 A
--------------------------	-----

##### Endurance

Electrical durability at nominal load in AC1 in operating cycles	50000
--	-------

##### Texts

Type of connection	With screw terminals
--------------------	----------------------

##### Power

Power loss at full load	1 W
-------------------------	-----

##### Settings

Programme cycles	Programme cycle: 24 hours
------------------	---------------------------