



VM11010

### Dual Row, 8 + 10 way 100A Switch Type 2 SPD

#### Technical Features

##### Installation, mounting

|             |                  |
|-------------|------------------|
| Mounting on | Surface mounting |
|-------------|------------------|

##### Architecture

|                 |   |
|-----------------|---|
| Number of poles | 2 |
|-----------------|---|

##### Functions

|                            |     |
|----------------------------|-----|
| Has protection main switch | Yes |
| Overvoltage protection     | No  |

##### Installation, mounting

|                            |    |
|----------------------------|----|
| Suitable for outdoor usage | No |
|----------------------------|----|

##### Capacity

|                   |    |
|-------------------|----|
| Number of modules | 18 |
|-------------------|----|

##### Electric current

|               |       |
|---------------|-------|
| Rated current | 100 A |
|---------------|-------|

##### Dimensions

|                       |           |
|-----------------------|-----------|
| Depth                 | 102.50 mm |
| Height                | 480 mm    |
| Width                 | 293 mm    |
| Thickness of sidewall | 1 mm      |

##### Cover, door

|                           |    |
|---------------------------|----|
| Interlockable             | No |
| Door/cover is transparent | No |

##### Materials

|          |            |
|----------|------------|
| RAL code | 9010       |
| Colour   | Pure white |
| Material | Steel      |

##### Connection

|                             |   |
|-----------------------------|---|
| Number of accessible phases | 1 |
|-----------------------------|---|

##### Scope of delivery

|                             |   |
|-----------------------------|---|
| Number of RCCB in enclosure | 0 |
|-----------------------------|---|

##### Equipment

|                    |    |
|--------------------|----|
| Number of rows     | 2  |
| Number of rails    | 2  |
| Extension possible | No |
| With socket outlet | No |

##### Safety

|                                         |       |
|-----------------------------------------|-------|
| Impact resistance IK                    | IK05  |
| Ingress Protection (IP) class           | IP2XC |
| Number of earth leakage switches 300 mA | 0     |

##### Sustainability

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|