



HMD299

MCB 2P 15kA D-125A 3M

Technical Features

Architecture

| | |
|--------------|----|
| Type of pole | 2P |
| Curve | D |

Voltage

| | |
|---|-------------|
| Rated operational voltage U_e | 415 - 415 V |
| Type voltage supply | AC |
| Rated insulation voltage U_i | 500 V |
| Rated impulse withstand voltage U_{imp} | 6000 V |

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

Installation, mounting

| | |
|---|----------------|
| Nominal tightening torque | 3.5 - 5.0 Nm |
| Type of top connection for modular devices | Screw terminal |
| Type of bottom connection for modular devices | Screw terminal |

Electric current

| | |
|--|----------|
| Rated current | 125 A |
| Rated service breaking capacity I_{cs} AC according to IEC 60898-1 | 7.50 kA |
| Rated short-circuit breaking capacity I_{cn} under 230 V AC according to IEC 60898-1 | 15 kA |
| Rated ultimate short-circuit breaking capacity I_{cu} under 230 V AC IEC 60947-2 | 15 kA |
| Rated ultimate short-circuit breaking capacity I_{cu} under 400 V AC IEC 60947-2 | 15 kA |
| Rated current 30°C | 125 A |
| Rated current 35°C | 122 A |
| Rated current at 40°C | 119 A |
| Rated current at 45°C | 115.70 A |
| Rated current at 50°C | 112 A |
| Rated current 55°C | 109.10 A |
| Rated current 60°C | 105.60 A |

Main electrical attributes

| | |
|--|-------|
| Rated short-circuit breaking capacity I_{cn} AC according to IEC 60898-1 | 15 kA |
|--|-------|

Installation, mounting

| | |
|---|----------------|
| Nominal tightening torque down terminal | 3.60 - 3.60 Nm |
| Nominal tightening torque top terminal | 3.60 - 3.60 Nm |

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Power

| | |
|------------------------------|------|
| Total power loss under I_N | 21 W |
|------------------------------|------|

Endurance

| | |
|--|-------|
| Electric endurance in number of cycles | 4000 |
| Number of mechanical operations | 20000 |

Connection

| | |
|--|------------------------|
| Cross-section of input and output with screws, for massive conductors | 1 - 70 mm ² |
| Cross-section of input and output with screws, for flexible conductors | 1 - 50 mm ² |
| Cross-section flexible conductor | 50 mm ² |
| Cross-section rigid conductor | 70 mm ² |

Use conditions

| | |
|--|------------------|
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 3 |
| Air humidity protection | For all climates |
| Operating temperature | -25 - 70 °C |

Capacity

Number of modules 3

Connectivity

Top connection alignment for modular devices Aligned terminal

Down connection alignment for modular devices Aligned terminal

Dimensions

Height 90 mm

Width 53 mm

Depth 70 mm

Sustainability

REACH-SVHC free Yes

RoHS conform Yes

Illustrations | Drawings

