



HXA025H

Auxiliary low level 1NO+1NC 125V AC (x160-P160-x250-P250-x630-P630)

Technical Features

Electric current

Rated current 230 V AC15 0 A

Connectivity

Type of connection quickconnect

Mounting type Click mounting

Connection

Type of contacts 1NC+1NO

Voltage

Type voltage supply AC/DC

Power

Total power loss under IN 3 W

Equipment

Number of INV contacts 1

Number of NC contacts 0

Safety

Ingress Protection (IP) class IP4X

Sustainability

REACH-SVHC free Yes

RoHS conform Yes