



EPS410B



Electronic latching relay 1NO 230V

Technical Features

Electric current

| | |
|-------------------------------|--------|
| Rated current | 16 A |
| Quiescent current | 100 mA |
| Acceptable current rating AC1 | 16 A |

Capacity

| | |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

Connection

| | |
|----------------------------------|---------------------------|
| Type of contacts | 1NO |
| Cross-section flexible conductor | 1.5 - 2.5 mm ² |
| Cross-section rigid conductor | 1.5 - 2.5 mm ² |
| Number of contacts | 1 |

Voltage

| | |
|------------------------------|-------------|
| Command voltage AC | 230 - 230 V |
| Command voltage DC | 0 - 0 V |
| Command voltage 1 | 230 - 230 V |
| Rated operational voltage Ue | 230 - 230 V |

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

Use conditions

| | |
|-------------------------------|-------------|
| Operating temperature | -20 - 60 °C |
| Storage/transport temperature | -10 - 50 °C |

Connectivity

| | |
|--------------------|--------------|
| Type of connection | quickconnect |
|--------------------|--------------|

Power

| | |
|---------------------------|--------|
| Total power loss under IN | 1.20 W |
| Inrush power absorbed | 5 VA |

Dimensions

| | |
|--------|-------|
| Height | 85 mm |
| Width | 18 mm |
| Depth | 64 mm |

Lighting

| | |
|-------------------------------------------------|---------|
| Max. load fluorescent lamp | 1200 VA |
| Max. load fluorescent lamp parallel compensated | 300 VA |

Equipment

| | |
|-----------------------|---|
| Number of NO contacts | 1 |
| Number of NC contacts | 0 |

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|

Illustrations | Drawings

