



WMGS13LB

## 2 Way & Centre Off Latching Switch Black

### Technical Features

#### Electric current

Switching current	10 A
-------------------	------

#### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

#### Voltage

Rated voltage	250 V
---------------	-------

#### Materials

Colour	White
--------	-------

Surface finish	Glossy
----------------	--------

Material	Duroplastic
----------	-------------

Treatment	Untreated
-----------	-----------

#### Identification

Assembly arrangement	Basic element with central cover plate
----------------------	--

#### Connectivity

Mounting type	Snap-on mounting
---------------	------------------

#### Controls and indicators

Number of buttons	1
-------------------	---

#### Dimensions

Dimensions	59 x 25 mm
------------	------------

Built-in depth	13.10 mm
----------------	----------

#### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

#### Architecture

Control/operation element	Single rocker
---------------------------	---------------

#### Electric current

Rated current	10 A
---------------	------

#### Texts

Lighting	Without lighting (cannot be illuminated)
----------	--

Switch mode	2-pole
-------------	--------

#### Sustainability

Halogen free	Yes
--------------	-----

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----