



VT09S

Technical Features

Voltage

| | |
|-----------------|-------------|
| Nominal voltage | 230 - 415 V |
|-----------------|-------------|

Installation, mounting

| | |
|----------------------------|------------------|
| Suitable for outdoor usage | No |
| Mounting on | Surface mounting |

Equipment

| | |
|-----------------|---|
| Number of rails | 1 |
| Number of rows | 1 |

Capacity

| | |
|-------------------|---|
| Number of modules | 9 |
|-------------------|---|

Dimensions

| | |
|----------------|--------|
| Height | 250 mm |
| Width | 259 mm |
| Depth | 71 mm |
| Built-in depth | 70 mm |

Cover, door

| | |
|-----------------|---|
| Number of locks | 0 |
|-----------------|---|

Dimensions

| | |
|-----------------------|---|
| Number of width units | 9 |
|-----------------------|---|

Cover, door

| | |
|---------------------------|----|
| Door/cover is transparent | No |
|---------------------------|----|

Connection

| | |
|--------------------------|----|
| Number of conduit inlets | 16 |
|--------------------------|----|

Connectivity

| | |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

Materials

| | |
|----------|------------|
| Material | Steel |
| RAL code | 9002 |
| Colour | Grey white |

Safety

| | |
|----------------------|-------------------|
| Protection class | Isolation class I |
| Impact resistance IK | IK05 |

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform | Yes |