



HBA161H

Electronic earth leakage add-on block 4P 160A Idn adjustable, time delay

Technical Features

Electric current

| | |
|--------------------------------------|---------|
| Rated current | 160 A |
| Rated residual operating current Idn | 30 mA |
| | 100 mA |
| | 300 mA |
| | 1000 mA |
| | 3000 mA |
| | 6000 mA |

Architecture

| | |
|-----------------|---|
| Number of poles | 4 |
|-----------------|---|

Safety

| | |
|-----------------------|------|
| Residual current type | A HI |
|-----------------------|------|

Voltage

| | |
|--------------------------------------|--------|
| Rated insulation voltage Ui | 500 V |
| Rated impulse withstand voltage Uimp | 6000 V |

Connection

| | |
|--|----------------------------|
| Cross-section of input and output with screws, for massive conductors | 2.5 - 95.0 mm ² |
| Cross-section of input and output with screws, for flexible conductors | 2.5 - 70.0 mm ² |

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|