



SBN140

### 1-pole, 40A Modular Switch

#### Technical Features

##### Architecture

Number of poles	1
Neutral position	Without neutral
Type of pole	1P

##### Electric current

Rated current	40 A
Acceptable current rating AC21 category A	40 A
Acceptable current rating AC21 category B	40 A
Acceptable current rating AC22 category A	40 A
Acceptable current rating AC22 category B	40 A
Rated short-circuit making capacity Icm under 240 V AC according to IEC 60947-3	0.84 kA
Rated short-time withstand current Icw 1s IEC 60947	0.60 kA
Rated conditional short-circuit current Inc with fuse according to IEC/EN 60669-2-4	6000A/80A gG parallel 16A gG

##### Installation, mounting

Nominal tightening torque	2.80 - 2.80 Nm
---------------------------	----------------

##### Voltage

Rated operational voltage Ue	230 - 230 V
Type voltage supply	AC
Rated insulation voltage Ui	440 V
Rated impulse withstand voltage Uimp	6000 V

##### Capacity

Number of modules	1
-------------------	---

##### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Dimensions

Height	83 mm
Width	17.50 mm
Depth	68 mm
Dimensions	83 x 17.50 mm

##### Equipment

Number of NO contacts	1
Number of NC contacts	0

##### Use conditions

Operating temperature	-20 - 70 °C
Storage/transport temperature	-40 - 80 °C

##### Connection

Cross-section flexible conductor	2.5 - 16 mm²
Cross-section rigid conductor	2.5 - 25 mm²

##### Endurance

Number of mechanical operations	60000
Electrical durability at nominal load in AC21 in operating cycles	5000
Electrical durability at nominal load in AC22 in operating cycles	5000

<b>Power</b>	
Total power loss under I <sub>N</sub>	1.10 W
Power loss per pole at I <sub>N</sub>	1.10 W
<b>Connectivity</b>	
Top connection alignment for modular devices	Aligned terminal
<b>Sustainability</b>	
REACH-SVHC free	Yes
RoHS conform	Yes