



HHA048Z

**Moulded Case Circuit Breaker h3 x160 TM FIX 1P1D 50A 25kA CTC**

**Technical Features**

**Electric current**

Rated current	50 A
Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 240 V AC IEC 60947-2	25 kA
Rated service breaking capacity I <sub>cs</sub> under 230 V AC according to IEC 60947-2	20 kA
Rated current 10°C according to IEC 60947	61 A
Rated current 15°C according to IEC 60947	59.80 A
Rated current 20°C according to IEC 60947	58.50 A
Rated current 25°C according to IEC 60947	57.10 A
Rated current 30°C according to IEC 60947	55.80 A
Rated current at 35°C according to IEC 60947	54.40 A
Rated current at 40°C according to IEC 60947	52.90 A
Rated current 45°C according to IEC 60947	51.50 A
Rated current 50°C according to IEC 60947	50 A
Rated current 55°C according to IEC 60947	48.40 A
Rated current at 60°C according to IEC 60947	46.80 A
Rated current 65°C according to IEC 60947	45.10 A
Rated current 70°C according to IEC 60947	43.40 A

**Architecture**

Number of poles	1
Neutral position	Without neutral

**Tripping**

Response time when opening	10 ms
----------------------------	-------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Voltage**

Rated impulse withstand voltage U <sub>imp</sub>	8000 V
Rated insulation voltage U <sub>i</sub>	690 V

**Functions**

Trip unit	TM F/F
-----------	--------

**Power**

Total power loss under I <sub>N</sub>	5 W
---------------------------------------	-----

**Endurance**

Electric endurance in number of cycles	10000
Number of mechanical operations	20000

**Safety**

Ingress Protection (IP) class	IP4X
-------------------------------	------

**Connection**

Cross-section flexible conductor	4 - 70 mm <sup>2</sup>
Cross-section rigid conductor	4 - 95 mm <sup>2</sup>

**Connectivity**

Type of connection	Screw terminal
--------------------	----------------

**Settings**

Thermal protection knob setting xI <sub>N</sub>	1
	1

**Dimensions**

Height	130 mm
Width	25 mm
Depth	68 mm

---

**Compatibility**

---

Suitable for DIN Rail	No
-----------------------	----

---

**Main electrical attributes**

---

Magnetic protection trip time	0 - 0 ms
-------------------------------	----------

---

**Sustainability**

---

REACH-SVHC free	Yes
-----------------	-----

---

RoHS conform	Yes
--------------	-----

---