



SM102E

Multi-function measurement device

Technical Features

Frequency

Frequency 50 - 60 Hz

Dimensions

Height 96 mm

Width 96 mm

Depth 60 mm

Safety

Ingress Protection (IP) class IP51

Capacity

Number of modules 5

Use conditions

Operating temperature -10 - 55 °C

Storage/transport temperature -20 - 80 °C

Connectivity

Type of connection Screw terminal

Connection

Cross-section flexible conductor 2.5 - 6 mm²

Cross-section rigid conductor 2.5 - 6 mm²

Power

Total power loss under IN 10 W

Power consumption VA 10 VA

Equipment

Type of display LCD

Measurement

Frequency measuring range 45 - 65 Hz

Type of measuring instrument Multimeter

Current measurement range 0 - 9999 A

Installation, mounting

Mounting on Flush mounting
Surface mounting