



HES040NR

Moulded Case Circuit Breaker h3+ P160 Energy 3P3D 40A 70kA FTC

Technical Features

Electric current

Rated current	40 A
---------------	------

Architecture

Number of poles	3
Control/operation element	Toggle
Device construction type	Fixed built-in
Neutral position	Without neutral

Electric current

Rated ultimate short-circuit breaking capacity I _{cu} under 400 V AC IEC 60947-2	70 kA
Rated ultimate short-circuit breaking capacity I _{cu} under 240 V AC IEC 60947-2	85 kA
Rated ultimate short-circuit breaking capacity I _{cu} under 415 V AC IEC 60947-2	70 kA
Rated ultimate short-circuit breaking capacity I _{cu} under 690 V AC IEC 60947-2	6 kA
Rated service breaking capacity I _{cs} under 220 V AC according to IEC 60947-2	85 kA
Rated service breaking capacity I _{cs} under 230 V AC according to IEC 60947-2	85 kA
Rated service breaking capacity I _{cs} under 240 V AC according to IEC 60947-2	85 kA
Rated service breaking capacity I _{cs} under 380 V AC according to IEC 60947-2	50 kA
Rated service breaking capacity I _{cs} under 400 V AC according to IEC 60947-2	50 kA
Rated service breaking capacity I _{cs} under 415 V AC according to IEC 60947-2	50 kA
Rated service breaking capacity I _{cs} under 690 V AC according to IEC 60947-2	6 kA
Rated current 10°C according to IEC 60947	40 A
Rated current 15°C according to IEC 60947	40 A
Rated current 20°C according to IEC 60947	40 A
Rated current 25°C according to IEC 60947	40 A
Rated current 30°C according to IEC 60947	40 A
Rated current at 35°C according to IEC 60947	40 A
Rated current at 40°C according to IEC 60947	40 A
Rated current 45°C according to IEC 60947	40 A
Rated current 50°C according to IEC 60947	40 A
Rated current 55°C according to IEC 60947	40 A
Rated current at 60°C according to IEC 60947	40 A
Rated current 65°C according to IEC 60947	40 A
Rated current 70°C according to IEC 60947	40 A

Frequency

Frequency	50 - 60 Hz
-----------	------------

Voltage

Rated impulse withstand voltage U _{imp}	8000 V
Rated insulation voltage U _i	800 V
Rated operational voltage U _e	220 - 690 V

Power

Total power loss under I _N	1.68 W
---------------------------------------	--------

Functions

Trip unit	ENERGY
-----------	--------

Endurance

Electric endurance in number of cycles	10000
Number of mechanical operations	40000

Safety

Ingress Protection (IP) class	IP4X
-------------------------------	------

Installation, mounting

Nominal tightening torque	6 - 6 Nm
Mounting-/Connection Position	Front

Connection

Cross-section flexible conductor	6 - 70 mm ²
Cross-section rigid conductor	6 - 95 mm ²

Cover, door

Interlockable	Yes
---------------	-----

Cable

Cable material	Copper Aluminium
----------------	---------------------

Compatibility

Compatible with RDC AOB	No
Suitable for DIN Rail	No
Suitable for distribution board	Yes

Dimensions

Height	130 mm
Width	90 mm
Depth	97 mm

Settings

Adjustment range short-term delayed short-circuit release	24 - 400 A
---	------------

Electrical protection

Long-time overload protection (ltd): delay (tr)	0.5 s	
	1.5 s	
	2.5 s	
	5 s	
	7.5 s	
	9 s	
	10 s	
	12 s	
	14 s	
	16 s	
	Short-time protection (std): current (lsc)	1.5
		2
		2.5
3		
3.5		
4		
4.5		
5		
5.5		
6		
Short-time protection (std): delay (tsd)	6.5	
	7	
	7.5	
	8	
	8.5	
	9	
	9.5	
	10	
	Short-time protection (std): delay (tsd)	50 ms
		100 ms
200 ms		
300 ms		
	400 ms	

Electrical protection

Instantaneous protection (Ii): dial setting coefficient	3
	3.5
	4
	4.5
	5
	5.5
	6
	6.5
	7
	7.5
	8
	8.5
	9
	9.5
	10
	10.5
	11
	11.5
	12
	12.5
	13
	13.5
	14
	14.5
	15

Sustainability

RoHS conform	Yes
--------------	-----