



HDA023Z

### Moulded Case Circuit Breaker h3 x160 TM FIX 1P1D 25A 18kA CTC

#### Technical Features

##### Electric current

Rated current	25 A
Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 240 V AC IEC 60947-2	18 kA
Rated service breaking capacity I <sub>cs</sub> under 230 V AC according to IEC 60947-2	18 kA
Rated current 10°C according to IEC 60947	29.60 A
Rated current 15°C according to IEC 60947	29 A
Rated current 20°C according to IEC 60947	28.50 A
Rated current 25°C according to IEC 60947	27.90 A
Rated current 30°C according to IEC 60947	27.40 A
Rated current at 35°C according to IEC 60947	26.80 A
Rated current at 40°C according to IEC 60947	26.20 A
Rated current 45°C according to IEC 60947	25.60 A
Rated current 50°C according to IEC 60947	25 A
Rated current 55°C according to IEC 60947	24.30 A
Rated current at 60°C according to IEC 60947	23.70 A
Rated current 65°C according to IEC 60947	23 A
Rated current 70°C according to IEC 60947	22.30 A

##### Architecture

Number of poles	1
Control/operation element	Toggle
Device construction type	Fixed built-in
Neutral position	Without neutral

##### Tripping

Response time when opening	10 ms
----------------------------	-------

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Voltage

Rated impulse withstand voltage U <sub>imp</sub>	8000 V
Rated insulation voltage U <sub>i</sub>	690 V

##### Functions

Trip unit	TM F/F
-----------	--------

##### Power

Total power loss under I <sub>N</sub>	4.30 W
---------------------------------------	--------

##### Endurance

Electric endurance in number of cycles	10000
Number of mechanical operations	20000

##### Safety

Ingress Protection (IP) class	IP4X
-------------------------------	------

##### Connection

Cross-section flexible conductor	6 - 70 mm <sup>2</sup>
Cross-section rigid conductor	6 - 95 mm <sup>2</sup>

##### Installation, mounting

Nominal tightening torque	6 - 6 Nm
Mounting-/Connection Position	Front

##### Connectivity

Type of connection	Screw terminal
--------------------	----------------

##### Cover, door

Interlockable	Yes
---------------	-----

#### Settings

Thermal protection knob setting xIN	1
	1

#### Cable

Cable material	Copper
----------------	--------

#### Dimensions

Height	130 mm
Width	25 mm
Depth	68 mm

#### Compatibility

Suitable for DIN Rail	Yes
-----------------------	-----

#### Installation, mounting

Nominal tightening torque down terminal	6 - 6 Nm
Nominal tightening torque top terminal	6 - 6 Nm

#### Main electrical attributes

Magnetic protection trip time	0 - 0 ms
-------------------------------	----------

#### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes