



HHT101JR

**Moulded Case Circuit Breaker h3+ P250 LSI 4P4D N0-50-100% 100A 25kA FTC**

**Technical Features**

**Electric current**

Rated current	100 A
Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 230 V AC IEC 60947-2	35 kA
Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 240 V AC IEC 60947-2	35 kA
Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 400 V AC IEC 60947-2	25 kA
Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 415 V AC IEC 60947-2	25 kA
Breaking capacity on 1-pole for AC 230 V IEC 60947-2	2.50 kA
Breaking capacity on 1-pole for AC 400 V IEC 60947-2	2.50 kA

**Architecture**

Number of poles	4
Control/operation element	Toggle
Device construction type	Fixed built-in
Neutral position	Left

**Electric current**

Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 690 V AC IEC 60947-2	6 kA
Rated service breaking capacity I <sub>cs</sub> under 220 V AC according to IEC 60947-2	35 kA
Rated service breaking capacity I <sub>cs</sub> under 230 V AC according to IEC 60947-2	35 kA
Rated service breaking capacity I <sub>cs</sub> under 240 V AC according to IEC 60947-2	35 kA
Rated service breaking capacity I <sub>cs</sub> under 380 V AC according to IEC 60947-2	25 kA
Rated service breaking capacity I <sub>cs</sub> under 400 V AC according to IEC 60947-2	25 kA
Rated service breaking capacity I <sub>cs</sub> under 415 V AC according to IEC 60947-2	25 kA
Rated service breaking capacity I <sub>cs</sub> under 690 V AC according to IEC 60947-2	6 kA
Rated current 10°C according to IEC 60947	100 A
Rated current 15°C according to IEC 60947	100 A
Rated current 20°C according to IEC 60947	100 A
Rated current 25°C according to IEC 60947	100 A
Rated current 30°C according to IEC 60947	100 A
Rated current at 35°C according to IEC 60947	100 A
Rated current at 40°C according to IEC 60947	100 A
Rated current 45°C according to IEC 60947	100 A
Rated current 50°C according to IEC 60947	100 A
Rated current 55°C according to IEC 60947	100 A
Rated current at 60°C according to IEC 60947	100 A
Rated current 70°C according to IEC 60947	100 A
Rated current 65°C according to IEC 60947	100 A

**Settings**

Ir1 current dial setting	40 A
	45 A
	50 A
	57 A
	63 A
	72 A
	80 A
	87 A
	93 A
	100 A
Adjustment range short-term delayed short-circuit release	54.6 - 1000.0 A

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Installation, mounting**

Nominal tightening torque	12 - 12 Nm
Mounting-/Connection Position	Front

**Voltage**

Rated impulse withstand voltage Uimp	8000 V
Rated insulation voltage Ui	800 V
Rated operational voltage Ue	220 - 690 V

**Functions**

Trip unit	LSI
-----------	-----

**Power**

Total power loss under IN	7.20 W
Power loss per pole at In	2.40 W

**Endurance**

Electric endurance in number of cycles	10000
Number of mechanical operations	40000

**Equipment**

Number of auxiliary contacts as change-over contact	0
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0

**Safety**

Ingress Protection (IP) class	IP4X
-------------------------------	------

**Use conditions**

Operating temperature	-25 - 70 °C
-----------------------	-------------

**Connection**

Cross-section flexible conductor	35 - 150 mm <sup>2</sup>
----------------------------------	--------------------------

**Cover, door**

Interlockable	Yes
---------------	-----

**Connection**

Cross-section rigid conductor	35 - 185 mm <sup>2</sup>
Connector/plug type	Terminal

**Cable**

Cable material	Copper Aluminium
----------------	---------------------

**Use conditions**

Degree of pollution according to IEC 60664 / IEC 60947-2	3
--	---

**Dimensions**

Height	165 mm
Width	140 mm
Depth	97 mm

**Controls and indicators**

Motor drive integrated	No
------------------------	----

**Compatibility**

Suitable for DIN Rail	No
Compatible with RDC AOB	Yes
Suitable for distribution board	Yes

**Power supply**

Position power supply	Bidirectional
-----------------------	---------------

---

**Electrical protection**

Long-time overload protection (ltd): delay (tr)	0.5 s 1.5 s 2.5 s 5 s 7.5 s 9 s 10 s 14 s 16 s
Short-time protection (std): current (lsd)	1.5 2 3 4 5 6 7 8 10
Short-time protection (std): delay (tsd)	50 ms 100 ms 200 ms 300 ms 400 ms
Instantaneous protection (li): dial setting coefficient	3 4 5 6 7 8 10 12 15

---

**Sustainability**

RoHS conform	Yes
--------------	-----