



JK2B06S2

### Technical Features

#### Installation, mounting

|             |                  |
|-------------|------------------|
| Mounting on | Surface mounting |
|-------------|------------------|

#### Electric current

|                                   |      |
|-----------------------------------|------|
| Breaking and opening capacity Idm | 0 kA |
|-----------------------------------|------|

#### Equipment

|                        |                    |
|------------------------|--------------------|
| Has mounting plate     | No                 |
| Equipped with switch   | No switch          |
| Number of switches     | 0                  |
| Type of busbar chassis | Fixed load chassis |

#### Capacity

|                   |   |
|-------------------|---|
| Number of modules | 6 |
|-------------------|---|

#### Dimensions

|        |        |
|--------|--------|
| Height | 705 mm |
| Width  | 445 mm |
| Depth  | 125 mm |

#### Cover, door

|                           |    |
|---------------------------|----|
| Number of cabinet doors   | 1  |
| Door/cover is transparent | No |

#### Materials

|          |            |
|----------|------------|
| Material | Steel      |
| RAL code | 9002       |
| Colour   | Grey white |

#### Safety

|                               |                              |
|-------------------------------|------------------------------|
| Protection class              | Isolation class I            |
| Impact resistance IK          | IK05                         |
| Ingress Protection (IP) class | IP41                         |
| Locking type                  | Special tool<br>Without lock |

#### Architecture

|                 |    |
|-----------------|----|
| Number of poles | 18 |
|-----------------|----|

#### Sustainability

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|