



MBN132



**MCB 1P 6kA B-32A 1M**

**Technical Features**

**Electric current**

Rated current	32 A
Rated short-circuit breaking capacity I <sub>cn</sub> under 230 V AC according to IEC 60898-1	6 kA
Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 400 V AC IEC 60947-2	10 kA
Rated current -15°C	40.2 A
Rated current -10°C	39.6 A
Rated current -5°C	38.5 A
Rated current at 0°C	37.7 A
Rated current 5°C	36.9 A
Rated current 10°C	36.1 A
Rated current 15°C	35.2 A
Rated current at 20°C	34.4 A
Rated current 25°C	33.6 A
Rated current 30°C	32 A
Rated current 35°C	32 A
Rated current at 40°C	31.1 A
Rated current at 45°C	30.3 A
Rated current at 50°C	30 A
Rated current 55°C	28.7 A
Rated current 60°C	27.8 A
Rated current 65°C	27 A
Rated current 70°C	26.2 A

**Architecture**

Type of pole	1P
Curve	B

**Capacity**

Number of modules	1
-------------------	---

**Main electrical attributes**

Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1	6 kA
---	------

**Installation, mounting**

Nominal tightening torque top terminal	2.80 - 2.80 Nm
Nominal tightening torque down terminal	2.80 - 2.80 Nm

**Voltage**

Rated operational voltage U <sub>e</sub>	230 - 400 V
Type voltage supply	AC
Rated insulation voltage U <sub>i</sub>	500 V
Rated impulse withstand voltage U <sub>imp</sub>	4000 V

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Connection**

Cross-section of input and output with screws, for massive conductors	1 - 35 mm <sup>2</sup>
Cross-section of input and output with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for massive conductors	1 - 35 mm <sup>2</sup>
Cross-section flexible conductor	1 - 25 mm <sup>2</sup>
Cross-section rigid conductor	1 - 35 mm <sup>2</sup>

**Installation, mounting**

Nominal tightening torque	2.80 - 2.80 Nm
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal
360° mounting position possible	Yes

### Safety

Ingress Protection (IP) class	IP20
Grid distance	60 mm

### Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	2
Class of energy limitation I <sup>2</sup> t	3
Air humidity protection	For all climates
Operating temperature	-25 - +70 °C

### Power

Total power loss under IN	4.40 W
---------------------------	--------

### Connectivity

Type of connection	Screw terminal
Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal

### Dimensions

Height	83 mm
Width	17.50 mm
Depth	70 mm

### Sustainability

RoHS conform	Yes
--------------	-----

### Illustrations | Drawings

