



HAB406

Load break switch 4P 63A

Technical Features

Electric current

Rated current	63 A
Acceptable current rating AC21	63 A
Acceptable current rating AC21 category A	63 A
Acceptable current rating AC21 category B	63 A
Acceptable current rating AC22 category A	63 A

Architecture

Type of pole	4P
--------------	----

Electric current

Acceptable current rating AC22 category B	63 A
---	------

Architecture

Control/operation element	Short rotary handle
---------------------------	---------------------

Electric current

Acceptable current rating AC23 category A	40 A
Acceptable current rating AC23 category B	40 A

Architecture

Number of poles	4
-----------------	---

Electric current

Rated short-circuit making capacity I _{cm} under 415 V AC according to IEC 60947-3	1.50 kA
Rated short-time withstand current I _{cw} 1s IEC 60947	1.26 kA
Rated short-time withstand current I _{cw} IEC 60947	1.26 kA
Rated conditional short-circuit current I _{cc} with gl-gG fuses	50 kA

Connection

Cross-section rigid conductor	16 mm ²
-------------------------------	--------------------

Voltage

Rated insulation voltage U _i	800 V
Rated impulse withstand voltage U _{imp}	8000 V
Rated operational voltage U _e	380 - 415 V

Power

Power loss per pole at I _n	2.40 W
Total power loss under I _N	9.60 W
Rated operational power under 400 V AC AC1	41000 W
Rated operational power under 400 V AC AC23	28000 W

Installation, mounting

Nominal tightening torque	2 - 2.2 Nm
---------------------------	------------

Equipment

Motor drive optional	No
Number of auxiliary contacts as change-over contact	0
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0

Use conditions

Operating temperature	-20 - 70 °C
-----------------------	-------------

Cover, door

Interlockable	Yes
---------------	-----

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Frequency

Frequency 50 - 50 Hz

Connectivity

Type of connection Screw terminal

Functions

Is reversing switch No
Version as emergency stop installation No
Version as main switch Yes
Version as maintenance/service switch Yes
Version as safety switch Yes
Version as switch disconnecter compact Yes

Capacity

Number of modules 3.42

Sustainability

REACH-SVHC free Yes
RoHS conform Yes

Illustrations | Drawings

