



HWX020H

Shunt trip coil 24-30V AC/DC (SH)

Technical Features

Power

Inrush power absorbed	300 VA
Operating consumption	5 VA

Safety

Ingress Protection (IP) class	IP4X
-------------------------------	------

Use conditions

Operating temperature	-25 - 70 °C
-----------------------	-------------

Voltage

Command voltage AC	24 - 30 V
Command voltage DC	24 - 30 V
Rated insulation voltage Ui	480 V
Rated impulse withstand voltage Uimp	6000 V

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes