



HMJ500HR

### Moulded Case Circuit Breaker h3 x630 LSNI Fixed 3P3D 500A 50kA FTC

#### Technical Features

##### Electric current

Rated current	500 A
Rated ultimate short-circuit breaking capacity Icu under 230 V AC IEC 60947-2	85 kA
Rated ultimate short-circuit breaking capacity Icu under 240 V AC IEC 60947-2	85 kA
Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity Icu under 415 V AC IEC 60947-2	50 kA
Breaking capacity on 1-pole for AC 230 V IEC 60947-2	10 kA
Breaking capacity on 1-pole for AC 400 V IEC 60947-2	10 kA

##### Architecture

Number of poles	3
Control/operation element	Toggle
Device construction type	Fixed built-in
Neutral position	Without neutral

##### Tripping

Response time when opening	10 ms
----------------------------	-------

##### Electric current

Rated service breaking capacity Ics under 230 V AC according to IEC 60947-2	85 kA
Rated service breaking capacity Ics under 400 V AC according to IEC 60947-2	50 kA
Rated current 10°C according to IEC 60947	500 A
Rated current 15°C according to IEC 60947	500 A
Rated current 20°C according to IEC 60947	500 A
Rated current 25°C according to IEC 60947	500 A
Rated current 30°C according to IEC 60947	500 A
Rated current at 35°C according to IEC 60947	500 A
Rated current at 40°C according to IEC 60947	500 A
Rated current 45°C according to IEC 60947	500 A
Rated current 50°C according to IEC 60947	500 A
Rated current 55°C according to IEC 60947	500 A
Rated current at 60°C according to IEC 60947	500 A
Rated current 65°C according to IEC 60947	500 A
Rated current 70°C according to IEC 60947	500 A

##### Settings

Ir1 current dial setting	500 A
Adjustment range short-term delayed short-circuit release	5000 - 5000 A

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Installation, mounting

Nominal tightening torque	18 - 18 Nm
Mounting-/Connection Position	Front

##### Voltage

Rated impulse withstand voltage Uimp	8000 V
Rated insulation voltage Ui	800 V
Rated operational voltage Ue	220 - 415 V

##### Functions

Trip unit	LSNI
-----------	------

##### Power

Total power loss under IN	120 W
Power loss per pole at In	40 W

---

**Equipment**

Number of auxiliary contacts as change-over contact	0
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0

**Safety**

Ingress Protection (IP) class	IP4X
-------------------------------	------

**Use conditions**

Operating temperature	-25 - 70 °C
-----------------------	-------------

**Connection**

Connector/plug type	Terminal
---------------------	----------

**Cable**

Cable material	Copper Aluminium
----------------	---------------------

**Dimensions**

Height	260 mm
Width	140 mm
Depth	150 mm

**Controls and indicators**

Motor drive integrated	No
------------------------	----

**Compatibility**

Suitable for DIN Rail	No
Compatible with RDC AOB	Yes
Suitable for distribution board	Yes

**Power supply**

Position power supply	Bidirectional
-----------------------	---------------

**Electrical protection**

Long-time overload protection (ltd): delay (tr)	5 s
Short-time protection (std): current (Isd)	10
Short-time protection (std): delay (tsd)	100 ms
Instantaneous protection (li): dial setting coefficient	1