



WXF422V

**Double socket for trunking gallery 2P+E 16A green**

**Technical Features**

**Electric current**

Rated current	16 A
---------------	------

**Use conditions**

Operating temperature	-10 - 35 °C
-----------------------	-------------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Materials**

Colour	Green
RAL code	6024
Surface finish	Glossy
Material	Polycarbonate (PC)
Treatment	Untreated

**Dimensions**

Height	42.50 mm
Width	90 mm
Number of units	2
Built-in depth flush-mounted boxes	50 mm

**Installation, mounting**

Mounting on	Wall duct
-------------	-----------

**Connectivity**

Mounting type	Click mounting
---------------	----------------

**Equipment**

Connector/plug type socket outlet	French norm NF
Rotated central insert	Yes
With hinged lid	No
With round protective earth pin	Yes
With signal lamp	No

**Accessories**

Has labelling field	No
---------------------	----

**Capacity**

Number of modules	4
-------------------	---

**Safety**

With enhanced contact protection	Yes
Impact resistance IK	IK07
Ingress Protection (IP) class	IP20

**Functions**

With orientation lighting	No
With function lighting	No

**Identification**

With imprint	No
--------------	----

**Texts**

Cover	Complete housing
Protection	Enhanced contact protection

**Suitable for**

Desk module / gallery	
-----------------------	--

---

**Sustainability**

---

RoHS conform

Yes