



HAB306

**Load break switch 3P 63A**

**Technical Features**

**Electric current**

Rated current	63 A
Acceptable current rating AC21	63 A
Acceptable current rating AC21 category A	63 A
Acceptable current rating AC21 category B	63 A
Acceptable current rating AC22 category A	63 A

**Architecture**

Type of pole	3P
--------------	----

**Electric current**

Acceptable current rating AC22 category B	63 A
---	------

**Architecture**

Control/operation element	Short rotary handle
---------------------------	---------------------

**Electric current**

Acceptable current rating AC23 category A	40 A
Acceptable current rating AC23 category B	40 A

**Architecture**

Number of poles	3
-----------------	---

**Electric current**

Rated short-circuit making capacity $I_{cm}$ under 415 V AC according to IEC 60947-3	1.50 kA
Rated short-time withstand current $I_{cw}$ 1s IEC 60947	1.26 kA
Rated short-time withstand current $I_{cw}$ IEC 60947	1.26 kA
Rated conditional short-circuit current $I_{cc}$ with gl-gG fuses	50 kA

**Connection**

Cross-section rigid conductor	16 mm <sup>2</sup>
-------------------------------	--------------------

**Voltage**

Rated insulation voltage $U_i$	800 V
Rated impulse withstand voltage $U_{imp}$	8000 V
Rated operational voltage $U_e$	380 - 415 V

**Power**

Power loss per pole at $I_n$	2.40 W
Total power loss under $I_N$	7.20 W
Rated operational power under 400 V AC AC1	41000 W
Rated operational power under 400 V AC AC23	28000 W

**Installation, mounting**

Nominal tightening torque	2 - 2.2 Nm
---------------------------	------------

**Equipment**

Motor drive optional	No
Number of auxiliary contacts as change-over contact	0
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0

**Use conditions**

Operating temperature	-20 - 70 °C
-----------------------	-------------

**Cover, door**

Interlockable	Yes
---------------	-----

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

---

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

---

**Connectivity**

Type of connection	Screw terminal
--------------------	----------------

---

**Functions**

Is reversing switch	No
Version as emergency stop installation	No
Version as main switch	Yes
Version as maintenance/service switch	Yes
Version as safety switch	Yes
Version as switch disconnecter compact	Yes

---

**Capacity**

Number of modules	2.57
-------------------	------

---

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes

---