



EPN410

Electronic latching relay 1NO 230V

Technical Features

Electric current

Rated current	16 A
Quiescent current	100 mA
Acceptable current rating AC1	16 A

Capacity

Number of modules	1
-------------------	---

Connection

Type of contacts	1NO
Cross-section flexible conductor	1 - 6 mm ²
Cross-section rigid conductor	1 - 10 mm ²
Number of contacts	1

Voltage

Command voltage AC	230 - 230 V
Command voltage DC	0 - 0 V
Command voltage 1	230 - 230 V
Rated operational voltage Ue	250 - 250 V

Frequency

Frequency	50 - 60 Hz
-----------	------------

Use conditions

Operating temperature	-20 - 60 °C
Storage/transport temperature	-10 - 50 °C

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Power

Total power loss under IN	1.20 W
Inrush power absorbed	5 VA

Dimensions

Height	85 mm
Width	18 mm
Depth	60 mm

Lighting

Max. load fluorescent lamp	1000 VA
Max. load fluorescent lamp parallel compensated	300 VA

Equipment

Number of NO contacts	1
Number of NC contacts	0

Sustainability

REACH-SVHC free	Yes
-----------------	-----