



JK116BGSD

125A 16 Way TPN Board with 3 pole Switch Disconector

Technical Features

Installation, mounting

| | |
|-------------|------------------|
| Mounting on | Surface mounting |
|-------------|------------------|

Architecture

| | |
|-----------------|---|
| Number of poles | 3 |
|-----------------|---|

Functions

| | |
|----------------------------|-----|
| Has protection main switch | Yes |
| Overvoltage protection | No |

Installation, mounting

| | |
|----------------------------|----|
| Suitable for outdoor usage | No |
|----------------------------|----|

Capacity

| | |
|-------------------|----|
| Number of modules | 48 |
|-------------------|----|

Electric current

| | |
|---------------|-------|
| Rated current | 125 A |
|---------------|-------|

Dimensions

| | |
|-----------------------|-----------|
| Depth | 132.50 mm |
| Height | 950 mm |
| Width | 465 mm |
| Thickness of sidewall | 1.20 mm |

Cover, door

| | |
|---------------------------|-----|
| Interlockable | No |
| Door/cover is transparent | Yes |

Materials

| | |
|----------|------------|
| RAL code | 7035 |
| Colour | Light grey |
| Material | Steel |

Connection

| | |
|-----------------------------|---|
| Number of accessible phases | 3 |
|-----------------------------|---|

Equipment

| | |
|--------------------|-----|
| Extension possible | Yes |
| With socket outlet | No |

Safety

| | |
|---|------|
| Impact resistance IK | IK05 |
| Ingress Protection (IP) class | IP30 |
| Number of earth leakage switches 300 mA | 0 |

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|