



MU316A

**MCB 3P 6kA C-16A 3M**

**Technical Features**

**Electric current**

Rated current	16 A
Rated short-circuit breaking capacity I <sub>cn</sub> under 230 V AC according to IEC 60898-1	6 kA
Rated current -15°C	20.12 A
Rated current -10°C	19.71 A
Rated current -5°C	19.28 A
Rated current at 0°C	18.85 A
Rated current 5°C	18.40 A
Rated current 10°C	17.95 A
Rated current 15°C	17.48 A
Rated current at 20°C	17 A
Rated current 25°C	16.51 A
Rated current 30°C	16 A
Rated current 35°C	15.47 A
Rated current at 40°C	14.93 A
Rated current at 45°C	14.37 A
Rated current at 50°C	13.78 A
Rated current 55°C	13.16 A
Rated current 60°C	12.52 A
Rated current 65°C	11.84 A
Rated current 70°C	11.12 A

**Architecture**

Type of pole	3P
Curve	C

**Capacity**

Number of modules	3
-------------------	---

**Main electrical attributes**

Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1	6 kA
---	------

**Installation, mounting**

Nominal tightening torque top terminal	2.80 - 2.80 Nm
Nominal tightening torque down terminal	2.80 - 2.80 Nm

**Voltage**

Rated operational voltage U <sub>e</sub>	400 - 400 V
Type voltage supply	AC
Rated insulation voltage U <sub>i</sub>	500 V
Rated impulse withstand voltage U <sub>imp</sub>	4000 V

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Connection**

Cross-section of input and output with screws, for massive conductors	1 - 35 mm <sup>2</sup>
Cross-section of input and output with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for massive conductors	1 - 35 mm <sup>2</sup>
Cross-section flexible conductor	1 - 25 mm <sup>2</sup>
Cross-section rigid conductor	1 - 35 mm <sup>2</sup>

**Installation, mounting**

Nominal tightening torque	2.80 - 2.80 Nm
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal
360° mounting position possible	Yes

---

**Safety**

---

Ingress Protection (IP) class	IP20
-------------------------------	------

---

**Use conditions**

---

Degree of pollution according to IEC 60664 / IEC 60947-2	2
Class of energy limitation I <sup>2</sup> t	3
Air humidity protection	For all climates
Operating temperature	-25 - 70 °C

---

**Power**

---

Total power loss under IN	6.99 W
---------------------------	--------

---

**Connectivity**

---

Type of connection	Screw terminal
Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal

---

**Dimensions**

---

Height	83 mm
Width	52.50 mm
Depth	70 mm

---

**Sustainability**

---

RoHS conform	Yes
--------------	-----

---