



85345131



KNX radio motion det. comf 1.1 m quicklink, R.1/R.3/1930/R.cl., black glossy

Technical Features

Dimensions

| | |
|---------------------------------|---------------|
| Installation height | 1.10 - 1.10 m |
| Recommended installation height | 1.10 - 1.10 m |

Settings

| | |
|------------------------------|-----------|
| Supported configuration mode | quicklink |
| Minimal duty cycle | 1 s |

Functions

| | |
|--------------------|---------|
| Maximal duty cycle | 180 min |
|--------------------|---------|

Connectivity

| | |
|---------------------------|-----|
| With bus system KNX radio | Yes |
|---------------------------|-----|

Scope of delivery

| | |
|-------------------------|-----|
| Bus connection included | Yes |
|-------------------------|-----|

Lighting

| | |
|--------------------------------|-------------|
| Response brightness adjustable | 5 - 1000 lx |
|--------------------------------|-------------|

Detection

| | |
|----------------------------|-----------|
| Detection angle adjustable | 45 - 90 ° |
| Detection angle horizontal | 90 - 180 |

Use conditions

| | |
|-----------------------|------------|
| Operating temperature | -5 - 45 °C |
|-----------------------|------------|

Materials

| | |
|----------|---------------|
| Material | Thermoplastic |
|----------|---------------|

Texts

| | |
|----------|---|
| Function | Switch-off pre-warning on dimmer inserts With memory function for presence simulation Teach function for response brightness via button With keylock Party function for switching on for 2 hours Reset function (to factory setting) |
|----------|---|

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|