



JK2B12F2

**250A TP&N BOARD 12 WAY Flush enclosure**

**Technical Features**

**Connection**

Number of accessible phases	3
-----------------------------	---

**Installation, mounting**

Mounting on	Surface mounting
-------------	------------------

**Electric current**

Breaking and opening capacity ldm	0 kA
-----------------------------------	------

**Equipment**

Has mounting plate	No
--------------------	----

Equipped with switch	No switch
----------------------	-----------

Number of switches	0
--------------------	---

Type of busbar chassis	Fixed load chassis
------------------------	--------------------

**Capacity**

Number of modules	12
-------------------	----

**Dimensions**

Height	890 mm
--------	--------

Width	470 mm
-------	--------

Depth	5 mm
-------	------

**Cover, door**

Number of cabinet doors	1
-------------------------	---

Door/cover is transparent	No
---------------------------	----

**Materials**

Material	Steel
----------	-------

RAL code	9002
----------	------

Colour	Grey white
--------	------------

**Safety**

Protection class	Isolation class I
------------------	-------------------

Impact resistance IK	IK05
----------------------	------

Ingress Protection (IP) class	IP41
-------------------------------	------

Locking type	Special tool Without lock
--------------	------------------------------

**Architecture**

Number of poles	36
-----------------	----

**Sustainability**

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----