



SPB465R

Surge Protection Device 4P T2 TNS/TT Uc 320V In 20kA Imax 65kA remote contact

Technical Features

Capacity

Number of modules	4
-------------------	---

Voltage

Rated operational voltage Ue	240 - 415 V
Continuous operating voltage Uc according to IEC 61643-1	320 V
Voltage protection level Up according to IEC 61643-1	1.45 kV
Voltage protection level Up L-PE/N-PE according to IEC 61643-11	1.70 kV
Voltage level Up L-N/PEN IEC 61643-11	1450 V

Electric current

Nominal discharge current In 8 - 20 μs L-N(PEN)/N-PE IEC 61643	20 kA
Max. overcurrent protection device, parallel connection (fuse)	160 A
Max. discharge (Imax) L-N(PEN)/ N-PE	65 kA

Dimensions

Height	98.7 mm
Width	71.20 mm
Depth	77.5 mm

Use conditions

Operating temperature	-40 - 80 °C
-----------------------	-------------

Network configuration

Network type	TN-S TT
--------------	------------

Equipment

With remote signalling contact	Yes
--------------------------------	-----

Connection

Cross-section of input and output with screws, for flexible conductors	1.5 - 25.0 mm ²
Cross-section of input and output with screws, for massive conductors	1.5 - 35.0 mm ²
Cross-section signal contact	0.14 - 1.5 mm ²

Standards

Requirement class IEC 61643	T1 T2
-----------------------------	----------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Installation, mounting

Nominal tightening torque	3 - 3 Nm
---------------------------	----------

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes