



VML\_SIZE\_7

**16 Way HI Cf 100A Switch 2\*100A 30mA RCCB**

**Technical Features**

**Installation, mounting**

Mounting on	Surface mounting
-------------	------------------

**Functions**

Has protection main switch	Yes
----------------------------	-----

Overvoltage protection	Yes
------------------------	-----

**Capacity**

Number of modules	16
-------------------	----

**Electric current**

Rated current	100 A
---------------	-------

**Dimensions**

Depth	100 mm
-------	--------

Height	245 mm
--------	--------

Width	476 mm
-------	--------

**Cover, door**

Interlockable	No
---------------	----

Door/cover is transparent	No
---------------------------	----

**Materials**

RAL code	9010
----------	------

Colour	Pure white
--------	------------

Material	Steel
----------	-------

**Connection**

Number of accessible phases	1
-----------------------------	---

**Scope of delivery**

Number of earth leakage circuit breaker type A	2
--	---

Number of RCCB in enclosure	2
-----------------------------	---

**Equipment**

Number of rows	1
----------------	---

Number of rails	1
-----------------	---

**Safety**

Ingress Protection (IP) class	IP2XC
-------------------------------	-------

**Sustainability**

RoHS conform	Yes
--------------	-----