



TYFS120\_AVANT

**KNX/IP Secure interface, 1 module**

**Technical Features**

**Equipment**

Web server	No
------------	----

**Voltage**

Operating voltage	24 - 24 V
Operating voltage over bus	21 - 32 V
Type voltage supply	DC

**Settings**

Supported configuration mode	ETS
------------------------------	-----

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Equipment**

Number of channels	8
--------------------	---

**Use conditions**

Operating temperature	-5 - 45 °C
-----------------------	------------

**Controls and indicators**

With LED indication	Yes
---------------------	-----

**Dimensions**

Number of width units	1
-----------------------	---

**Connection**

Connector/plug type	RJ45
---------------------	------

**Texts**

Type of connection	Operating voltage connection via connecting terminal With RJ45 connection for Ethernet/IP networks
--------------------	---

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes