

Moulded Case Circuit Breaker h3 x160 TM FIX 2P2D 40A 25kA CTC

Technical Features

Electric current

Rated current I _N	40 A
Rated ultimate short-circuit breaking capacity I _{cu} under 400 V AC IEC 60947-2	25 kA
Rated ultimate short-circuit breaking capacity I _{cu} under 240 V AC IEC 60947-2	35 kA
Rated service breaking capacity I _{cs} under 230 V AC according to IEC 60947-2	25 kA
Rated service breaking capacity I _{cs} under 400 V AC according to IEC 60947-2	20 kA
Rated current at 10°C according to IEC 60947	49.50 A
Rated current at 15°C according to IEC 60947	48.40 A
Rated current at 20°C according to IEC 60947	47.30 A
Rated current at 25°C according to IEC 60947	46.10 A
Rated current at 30°C according to IEC 60947	45 A
Rated current at 35°C according to IEC 60947	43.80 A
Rated current at 40°C according to IEC 60947	42.50 A
Rated current at 45°C according to IEC 60947	41.30 A
Rated current at 50°C according to IEC 60947	40 A
Rated current at 55°C according to IEC 60947	38.60 A
Rated current at 60°C according to IEC 60947	37.20 A
Rated current at 65°C according to IEC 60947	35.70 A
Rated current at 70°C according to IEC 60947	34.20 A

Architecture

Number of poles	2
Neutral position	Without neutral

Tripping

Response time when opening	10 ms
----------------------------	-------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Voltage

Rated impulse withstand voltage U _{imp}	8000 V
Rated insulation voltage U _i	690 V
Rated operational voltage U _e	220 - 415 V

Functions

Trip unit	TM F/F
-----------	--------

Power

Power dissipation at I _N	7.30 W
-------------------------------------	--------

Endurance

Electric endurance in number of cycles	10000
Number of mechanical operations	20000

Safety

Ingress Protection (IP) class	IP4X
-------------------------------	------

Connection

Cross-section flexible conductor	4 - 70 mm ²
Cross-section rigid conductor	4 - 95 mm ²

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Settings

Thermal protection knob setting xI _N	1
	1

Dimensions		
Height		130 mm
Width		50 mm
Depth		68 mm
Compatibility		
Suitable for DIN Rail		No
Main electrical attributes		
Magnetic protection trip time		0 - 0 ms
Sustainability		
REACH-SVHC free		Yes
RoHS conform		Yes