



NBN416A

## MCB 4P 10kA B-16A 4M

### Technical Features

#### Electric current

Rated current	16 A
Rated service breaking capacity Ics under 230 V AC according to IEC 60947-2	15 kA
Rated short-circuit breaking capacity Icn under 230 V AC according to IEC 60898-1	10 kA
Rated ultimate short-circuit breaking capacity Icu under 230 V AC IEC 60947-2	30 kA
Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2	15 kA
Rated current -25°C	20.27 A
Rated current at -20°C	19.92 A
Rated current -15°C	19.56 A
Rated current -10°C	19.20 A
Rated current -5°C	18.83 A
Rated current at 0°C	18.45 A
Rated current 5°C	18.07 A
Rated current 10°C	17.67 A
Rated current 15°C	17.27 A
Rated current at 20°C	16.86 A
Rated current 25°C	16.43 A
Rated current 30°C	16 A
Rated current 35°C	15.48 A
Rated current at 40°C	14.94 A
Rated current at 45°C	14.38 A
Rated current at 50°C	13.80 A
Rated current 55°C	13.19 A
Rated current 60°C	12.56 A
Rated current 65°C	11.89 A
Rated current 70°C	11.18 A

#### Architecture

Type of pole	4P
Curve	B

#### Capacity

Number of modules	4
-------------------	---

#### Main electrical attributes

Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	10 kA
---	-------

#### Installation, mounting

Nominal tightening torque top terminal	2.80 - 2.80 Nm
Nominal tightening torque down terminal	2.80 - 2.80 Nm

#### Voltage

Rated operational voltage Ue	400 - 400 V
Type voltage supply	AC
Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	6000 V

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Connection

Cross-section of input and output with screws, for massive conductors	1 - 35 mm <sup>2</sup>
Cross-section of input and output with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for massive conductors	1 - 35 mm <sup>2</sup>
Cross-section flexible conductor	1 - 25 mm <sup>2</sup>
Cross-section rigid conductor	1 - 35 mm <sup>2</sup>

# Product Datasheet

## NBN416A

---

### Installation, mounting

Nominal tightening torque	2.80 - 2.80 Nm
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal

### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

### Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	2
Class of energy limitation I <sup>2</sup> t	3
Air humidity protection	For all climates
Operating temperature	-25 - 70 °C

### Power

Total power loss under IN	11.08 W
---------------------------	---------

### Endurance

Electric endurance in number of cycles	4000
Number of mechanical operations	200000

### Connectivity

Type of connection	Screw terminal
Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal

### Dimensions

Height	83 mm
Width	70 mm
Depth	70 mm