




ADC920R

RCBO 1M 1P+N 6kA C-20A 30mA typ A

Technical Features

Architecture

Type of pole	1P+N
Curve	C

Electric current

Rated current	20 A
Rated residual operating current I_{dn}	30 mA
Rated current -25°C	25.50 A
Rated current at -20°C	25 A
Rated current -15°C	24.50 A
Rated current -10°C	24 A
Rated current -5°C	23.50 A
Rated current at 0°C	23 A
Rated current 5°C	22.50 A
Rated current 10°C	22 A
Rated current 15°C	21.50 A
Rated current at 20°C	21 A
Rated current 25°C	20.50 A
Rated current 30°C	20 A
Rated current 35°C	19.60 A
Rated current at 40°C	19.20 A
Rated current at 50°C	18.40 A
Rated current 55°C	18 A
Rated current 60°C	17.60 A
Min./max. threshold value of the AC thermal operation	1.13 - 1.45 A

Safety

Residual current type	A
Ingress Protection (IP) class	IP20

Main electrical attributes

Rated short-circuit breaking capacity I_{cn} AC according to IEC 60898-1	6 kA
--	------

Voltage

Rated insulation voltage U_i	440 V
Rated impulse withstand voltage U_{imp}	4000 V
Max. operating voltage	264 V
Rated operational voltage U_e	230 - 230 V
Overvoltage category according to IEC 60947-1	3

Power

Total power loss under I_N	11.68 W
------------------------------	---------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Use conditions

Max. altitude	2000 m
Class of energy limitation I^2t	3

Connection

Cross-section of input with screws, for flexible conductors	1 - 10 mm ²
Cross-section of input with screws, for massive conductors	1 - 16 mm ²

Capacity

Number of modules	1
-------------------	---

Installation, mounting

Type of top connection for modular devices	Screw terminal
--	----------------

Installation, mounting

Type of bottom connection for modular devices	biconnect
---	-----------

Dimensions

Height	85 mm
Width	17.70 mm
Depth	70 mm

Use conditions

Operating temperature	-25 - 70 °C
Storage/transport temperature	-25 - 80 °C

Connection

Cross-section of input and output with screws, for flexible conductors	1 - 10 mm ²
Cross-section of input and output with screws, for massive conductors	1 - 16 mm ²

Compatibility

Suitable for DIN Rail	Yes
-----------------------	-----

Sustainability

RoHS conform	Yes
--------------	-----