



WBQSV2-MB

**FIN 2 Gang Switch Plate cw mechs MB**

**Technical Features**

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Materials**

Colour	Black
--------	-------

**Identification**

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

**Connectivity**

Mounting type	Screw mounting
---------------	----------------

**Controls and indicators**

Number of buttons	2
-------------------	---

**Dimensions**

Dimensions	117 x 77 mm
------------	-------------

**Safety**

Ingress Protection (IP) class	IP2X
-------------------------------	------

**Electric current**

Rated current	16 A
---------------	------

**Texts**

Installation mode	For screw fastening
-------------------	---------------------

Type of connection	With screw terminals
--------------------	----------------------

Lighting	Without lighting (cannot be illuminated)
----------	--

Switch mode	2-way, with loop terminal
-------------	---------------------------

**Sustainability**

Halogen free	Yes
--------------	-----

RoHS conform	Yes
--------------	-----