



WMGKSIEL

20A Double Pole Key Switch Marked 'EM LTG TEST'

Technical Features

Electric current

Momentary contact current	10 A
---------------------------	------

Voltage

Rated voltage	250 V
---------------	-------

Architecture

Control/operation element	Single rocker
Number of poles	2

Materials

Colour	White
Surface finish	Glossy
Material	Urea formaldehyde
Treatment	Untreated
Transparent	No

Dimensions

Height	60 mm
Width	25 mm
Depth	24 mm

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Controls and indicators

Number of buttons	0
With feedback signal contact	No

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Accessories

Has labelling field	No
---------------------	----

Texts

Imprint	With imprint
Lighting	Without neon lamp

Suitable for

sollysta	
----------	--

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes