




EHN111



### Daily time switch 1 channel, 3 modules with reserve

#### Technical Features

##### Equipment

Number of channels	1
--------------------	---

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Power

Power consumption during operation	0.50 W
230 V incandescent and halogen lamp	1100 W
Power incandescent lamp	900 - 900 W

##### Functions

Number of function channels	1
-----------------------------	---

##### Connection

Number of contacts	1
Cross-section flexible conductor	0.5 - 6 mm <sup>2</sup>
Cross-section rigid conductor	0.5 - 6 mm <sup>2</sup>

##### Use conditions

Operating temperature	-10 - +55 °C
-----------------------	--------------

##### Capacity

Number of modules	3
-------------------	---

##### Dimensions

Height	90 mm
Width	54 mm
Depth	60 mm

##### Texts

Switch mode	Change-over contact
Installation mode	For mounting on DIN rail

##### Electric current

Max. power (cos phi 0,6)	3 A
--------------------------	-----

##### Endurance

Electrical durability at nominal load in AC1 in operating cycles	50000
--	-------

##### Texts

Type of connection	With screw terminals
--------------------	----------------------

##### Voltage

Rated operational voltage U <sub>e</sub>	230 - 240 V
--	-------------

##### Power

Power loss at full load	1 W
-------------------------	-----

##### Settings

Programme cycles	Programme cycle: 24 hours
Shortest switching time	15 min

##### Lighting

LED lamp power	180 W
----------------	-------

##### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes