



LS502

Fuse carrier 2P 32A 690V L38 2M

Technical Features

Dimensions

Height	83 mm
Width	36 mm
Depth	75 mm

Architecture

Number of poles	2
-----------------	---

Electric current

Rated current	32 A
---------------	------

Capacity

Number of modules	2
-------------------	---

Use conditions

Operating temperature	-5 - 50 °C
-----------------------	------------

Installation, mounting

Nominal tightening torque	2.20 - 2.20 Nm
Mounting on	DIN rail

Power

Total power loss under IN	7.40 W
---------------------------	--------

Voltage

Rated insulation voltage Ui	690 V
Type voltage supply	AC

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Connection

Cross-section of input and output with screws, for flexible conductors	0.75 - 16 mm ²
Cross-section of input and output with screws, for massive conductors	1 - 25 mm ²

Fuse

Fuse size	10 x 38
-----------	---------

Cover, door

Interlockable	Yes
---------------	-----

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes

Illustrations | Drawings

