



LS501

Fuse 1P 32A 690V L38 1M

Technical Features

Dimensions

| | |
|--------|-------|
| Height | 83 mm |
| Width | 18 mm |
| Depth | 75 mm |

Architecture

| | |
|-----------------|---|
| Number of poles | 1 |
|-----------------|---|

Electric current

| | |
|---------------|------|
| Rated current | 32 A |
|---------------|------|

Capacity

| | |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

Use conditions

| | |
|-----------------------|------------|
| Operating temperature | -5 - 50 °C |
|-----------------------|------------|

Installation, mounting

| | |
|---------------------------|----------------|
| Nominal tightening torque | 2.20 - 2.20 Nm |
| Mounting on | DIN rail |

Power

| | |
|---------------------------|--------|
| Total power loss under IN | 7.40 W |
|---------------------------|--------|

Voltage

| | |
|-----------------------------|-------|
| Rated insulation voltage Ui | 690 V |
| Type voltage supply | AC |

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Connection

| | |
|--|---------------------------|
| Cross-section of input and output with screws, for flexible conductors | 0.75 - 16 mm ² |
| Cross-section of input and output with screws, for massive conductors | 1 - 25 mm ² |

Fuse

| | |
|-----------|---------|
| Fuse size | 10 x 38 |
|-----------|---------|

Cover, door

| | |
|---------------|-----|
| Interlockable | Yes |
|---------------|-----|

Illustrations | Drawings

